



Version: 15 April 2019

# PLATUNA<sup>®</sup>- ALLOY 1

## PLATINUM RUTHENIUM ELECTROLYTE



### Extraordinarily Abrasion-Resistant Coatings – Saving Platinum

PLATUNA<sup>®</sup>-Alloy 1 is used for depositing smooth, ultra-bright and extraordinarily abrasion-resistant platinum-ruthenium alloy coatings. The acidic electrolyte is used for decorative applications and guarantees light, white layers - crack-free up to 1  $\mu\text{m}$ .

PLATUNA<sup>®</sup>-Alloy 1 works across a wide operating range and reaches an excellent covering speed. It is used for rack operation.



### Advantages

- Acidic platinum alloy electrolyte - saves expensive platinum
- Light, white and ultra-bright coatings
- For decorative applications
- Extraordinarily abrasion-resistant
- Wide operating range
- Up to 1  $\mu\text{m}$  layer thickness (crack-free)
- The coatings are RoHS compliant
- Suitable for racks

### Applications

- Jewellery
- Writing implements
- Watches
- Spectacle frames
- Accessories

# PLATUNA®-ALLOY 1

## PLATINUM RUTHENIUM ELECTROLYTE




### TECHNICAL SPECIFICATIONS

Electrolyte characteristics	
Electrolyte type	Strongly acidic
Metal content	1.0 (0.8 - 1.2) g/l Pt 1.0 (0.8 - 1.2) g/l Ru
pH value	< 1
Operating temperature	35 (30 - 40) °C
Current density range	2.0 (0.5 - 5.0) A/dm <sup>2</sup>
Plating speed	Approx. 0.08 µm/ min at 2.0 A/dm <sup>2</sup>
Anode material	MMO (type PLATINODE® 187 SO)

Coating characteristics	
Coating	Platinum-ruthenium
Alloy composition	75 weight % Pt 25 weight % Ru
Colour of deposit	White
Brightness	Bright
Hardness of deposit HV 0.015 (Vickers) approx. values	Not measurable, Approx. 500 HV
Max. coating thickness	1.0 µm
Density of the coating	Approx. 19.16 g/cm <sup>3</sup>

#### Bosch-Weinmann Wear Test



### YOUR CONTACT

Do you have a specific question or would you like a no-obligation quote calculation? Our specialist will be happy to help you with any technical questions you might have.



**Markus Legeler**

Manager Sales International Support: Phone +49 7171 607-305

Sales Department: Phone +49 7171 607-204

Mail: [markus.legeler@eu.umicore.com](mailto:markus.legeler@eu.umicore.com)

Phone: +49 (0) 7171 607 - 204

